

## Arteor™ hotel equipment

square version – call indicators, illuminated signs, buzzers



Support frames and surround plates selection charts **p. 32-35**

Mechanisms supplied with white or magnesium square rocker plates  
To be equipped with support frames **p. 31** and surround plates **p. 32-45**

Pack	Cat. Nos.	Hotel bedroom call indicators
5	White 5720 57   Magnesium 5725 57	<p>Enables the resident to inform hotel staff of the room status Two settings are possible : - Do not disturb - Please clean the room 1 + 1 modules 22.5 x 45 mm</p> <p><b>Indicator</b>  Indicator lamp and bell push Installed in the corridor, display calls Supplied with LEDs</p>
5	5720 54   5725 54	<p><b>Internal control unit</b>  Allows the user to select the desired setting Supplied with LEDs</p>

Pack	Cat. Nos.	Illuminated signs
5	White 5722 24   Magnesium 5727 24	<p>Mechanisms integrating LEDs and a pivoting window that can take customised labels (printed using a simple text editor on transparent printing paper) 2 modules 22.5 x 45 mm</p> <p><b>Green or Red</b>  Sign with 2-state LEDs with choice of green or red configurable on the mechanism 1 W</p>
5	5722 25   5727 22	<p><b>Blue</b>  Sign with blue LED A choice of 2 power levels : 0.2 or 1 W</p>

Pack	Cat. Nos.	Buzzers
10	White 5722 07   Magnesium 5722 47	<p> 230 V 2 modules 22.5 x 45 mm</p>

## Arteor™ hotel equipment

round version – call indicators, illuminated signs, buzzers



Support frames and surround plates selection charts **p. 32-35**

Mechanisms supplied with white or magnesium round rocker plates  
To be equipped with support frames **p. 31** and surround plates **p. 32-45**

Pack	Cat. Nos.	Hotel bedroom call indicators
5	White 5720 67   Magnesium 5725 67	<p>Enables the resident to inform hotel staff of the room status Two settings are possible : - Do not disturb - Please clean the room 1 + 1 modules 22.5 x 45 mm</p> <p><b>Indicator</b>  Indicator lamp and bell push Installed in the corridor, display calls Supplied with LEDs</p>
5	5720 74   5725 74	<p><b>Internal control unit</b>  Allows the user to select the desired setting Supplied with LEDs</p>

Pack	Cat. Nos.	Illuminated signs
5	Magnesium 5727 25	<p>Mechanisms integrating LEDs and a pivoting window that can take customised labels (printed using a simple text editor on transparent printing paper) 2 modules 22.5 x 45 mm</p> <p><b>Green or Red</b>  Sign with 2-state LEDs with choice of green or red configurable on the mechanism 1 W</p>
5	5727 23	<p><b>Blue</b>  Sign with blue LED A choice of 2 power levels : 0.2 or 1 W</p>

Pack	Cat. Nos.	Buzzers
10	White 5722 08   Magnesium 5722 48	<p> 230 V 2 modules 22.5 x 45 mm</p>

## Arteor™ USB chargers

square version



5720 78



5720 71

Technical information **p. 23**  
Support frames and surround plates selection charts **p. 32-35**

Mechanisms supplied with rocker plates, to be equipped with support frames **p. 31** and surround plates **p. 32-35**

Average charging time for devices equipped with lithium-ion polymer batteries :

- 80 % charged < 2 h
- 100 % charged < 4 h

No specific constraint : no need to wait for the battery to be flat before charging, or to have it fully charged before use

Pack	Cat. Nos.	USB power supplies		
5/1	<table border="1"> <tr> <td>White 5720 78</td> <td>Magnesium 5725 78</td> </tr> </table>	White 5720 78	Magnesium 5725 78	<p>For recharging portable devices Conform to IEC 62684-2011-01 Consumption in passive mode &lt; 0.3 W 2P + E tap-off connection via 2.5 mm<sup>2</sup> screw terminals Supplied cordless</p> <p><b>Double USB sockets - 5 V - 1500 mA</b> For fast-charging telephones, smartphones, MP3/MP4 players and tablet PC</p> 2 modules
White 5720 78	Magnesium 5725 78			
10	5720 71   5725 71	<p><b>Single USB sockets - 5 V - 750 mA</b> For Smartphone</p> 1 module		
1	0803 99	<p><b>Support for portable device on charge</b></p> <p>Prevents device from any fall risk and allows secure use of device while charging Wall mounting Fixing tools supplied</p> For 1 portable device		

## Arteor™ USB chargers

round version



5724 88

Technical information **p. 23**  
Support frames and surround plates selection charts **p. 32-35**

Mechanisms supplied with rocker plates, to be equipped with support frames **p. 31** and surround plates **p. 32-35**

Average charging time for devices equipped with lithium-ion polymer batteries :

- 80 % charged < 2 h
- 100 % charged < 4 h

No specific constraint : no need to wait for the battery to be flat before charging, or to have it fully charged before use

Pack	Cat. Nos.	USB power supplies		
1	<table border="1"> <tr> <td>White 5724 88</td> <td>Magnesium 5733 98</td> </tr> </table>	White 5724 88	Magnesium 5733 98	<p>For recharging portable devices Conform to IEC 62684-2011-01 Consumption in passive mode &lt; 0.3 W 2P + E tap-off connection via 2.5 mm<sup>2</sup> screw terminals Supplied cordless</p> <p><b>Double USB sockets - 5 V - 1500 mA</b> For fast-charging telephones, smartphones, MP3/MP4 players and tablet PC</p> 2 modules
White 5724 88	Magnesium 5733 98			
1	0803 99	<p><b>Support for portable device on charge</b></p> <p>Prevents device from any fall risk and allows secure use of device while charging Wall mounting Fixing tools supplied</p> For 1 portable device		

Download the full file at

<http://assets.kempstoncontrols.com/doc/Wiring%20Accessories%20Product%20Guide.pdf>



**KEMPSTON**  
CONTROLS